



WIDEX CONSUMER GUIDE TO DIGITAL HEARING INSTRUMENTS



100% Digital Hearing Aid Styles



Widex Fully Digital Hearing Aid Technology

Widex offers a complete selection of 100% digital hearing instruments for all types of hearing losses, including the following:

widex mind[™]440

Dual ISP

Ultimate Performance in Noise

Next generation Dual Integrated Signal Processing (Dual ISP) technology
High Definition Locator Microphone
Speech Enhancer
TruSound Stabilizer
TruSound AOC

Ultimate Listening Comfort in Noise

Noise Reduction System
Wind Noise Reduction
TruSound Stabilizer
Up to 5 Customized Listening Programs

Ultimate Sound Quality

107 dB Extended Input Dynamic Range
15 Channel Processing
TruSound Compression
Soft Sounds Are Audible, Loud Sounds Are Not Uncomfortable.

Ultimate High Pitch Hearing

The unique Audibility Extender moves higher-pitched sounds that cannot be heard into lower-pitched regions of usable hearing. The algorithm offers a full range of adjustment so it may be fit precisely to more individuals.

Ultimate Storage of Use Information

Sound Diary II Improves Fitting and Use of Hearing Aids

Ultimate in Stopping Hearing Aid Whistling... Almost Everywhere

Multi-Directional Active Feedback Cancellation

Ultimate Hearing of Soft and Distant Speech

0 dB HL compression threshold

Ultimate in User-Friendliness

Zen relaxation program
SmartSpeak (and SmartTone)
Optional Remote Control and Volume Control

Ultimate in Battery Life

Excellent Telephone Coil Sensitivity

widex mind[™]330

Dual ISP

Exceptional Performance in Noise

Next generation Dual Integrated Signal Processing (Dual ISP)
High Definition Locator Microphone

Exceptional Listening Comfort in Noise

Noise Reduction System
Wind Noise Reduction
Up to 4 Customized Listening Programs

Exceptional Sound Quality

107 dB Extended Input Dynamic Range
10 Channel Processing
Soft Sounds Are Audible, Loud Sounds Are Not Uncomfortable.

Exceptional High Pitch Hearing

The unique Audibility Extender moves higher-pitched sounds that cannot be heard into lower-pitched regions of usable hearing.

Exceptional Storage of Use Information

Sound Diary II Improves Fitting and Use Of Hearing Aids

Exceptional in Stopping Hearing Aid Whistling... Almost Everywhere

Multi-Directional Active Feedback Cancellation

Exceptional Hearing of Soft and Distant Speech

0 dB HL compression threshold

Exceptional User-Friendliness

SmartSpeak (and SmartTone)
Optional Remote Control and Volume Control

Exceptional Battery Life

Excellent Telephone Coil Sensitivity

widex mind[™]220

Dual ISP

Outstanding Performance in Noise

Dual Integrated Signal Processing (Dual ISP)
High Definition Locator Microphone

Outstanding Listening Comfort in Noise

Noise Reduction System
Wind Noise Reduction
Up to 3 Customized Listening Programs

Outstanding Sound Quality

5 Channel Processing
Soft Sounds are Audible, Loud Sounds are not Uncomfortable

Outstanding High Pitch Hearing

Audibility Extender

Outstanding Storage of Use Information

Sound Diary II Improves Fitting and Use Of Hearing Aids

Outstanding in Stopping Hearing Aid Whistling... Almost Everywhere

Multi-Directional Active Feedback Cancellation

Outstanding User-Friendliness

SmartSpeak (and SmartTone)
Optional Remote Control and Volume Control

Outstanding Battery Life

EcoTech II

Outstanding Telephone Coil Sensitivity

widex  real[™]

ISP

Very Good Performance in Noise

Use of Integrated Signal Processing (ISP)
REAL Locator Microphone

Very Good Listening Comfort in Noise

Noise Reduction System
Wind Noise Reduction
Up to 3 Customized Listening Programs

Very Good Sound Quality

107 dB Extended Input Dynamic Range
3 Channel Processing
Soft Sounds Are Audible, Loud Sounds Are Not Uncomfortable.

No Hearing Aid Whistling in Almost All Listening Situations

Active Feedback Cancellation

Very Good Hearing of Soft and Distant Speech

0 dB HL compression threshold

Excellent Battery Life

Excellent Telephone Coil Sensitivity

WIDEX[®]

HIGH DEFINITION HEARING

www.widexusa.com